

Three adjustable shelves. Overall Dimensions To unlock the cart with the electronic keypad, enter your User or Supervisor pin and press "En-ter". Product No: PEL-Color Price: Call for Pricing US Shipping and Billing Only AluminumDrawer Auto-Locking Cart, in. Browse their catalog to find the The NEW Aluminum Wireless Auto-Locking Cart from Armstrong Medical features keyless entry, an LCD display (shows date, time of day, current battery life, and programmable Missing: pdf Standard 5" locking and swivel, heavy-duty casters and a built-in stabilizer bumper give Armstrong carts mobility and stability, pluscolors to choose from (from top to bottom capabilities include all the features of the Auto-Locking Carts. Armstrong Medical is a leading medical equipment and supply company that offers a wide range of products for various healthcare settings. Cart size"W x"L x/2"H. This document is available from Sign up or Missing: pdf View & download of more than Armstrong PDF user manuals, service manuals, operating guides. Water Pump, Control Unit user manuals, operating guides & Premier Aluminum Solid Color Anesthesia Carts Procedure Carts Mobile g: pdfACWGeneral Purpose Wire Push Cart, \$ These versatile carts feature three" x" shelves that can be adjusted or removed to suit your needs. Four 5" rubber casters. If an incorrect number is pushed while entering in your pin, press "Clear" and start over. NOTE: If you wish to use your current HIDTM cards, each card must be made available to be programmed Manufacturer: Armstrong Medical Industries Inc. Model: APB-AA Model Description: Steel Push-Button Locking Anesthesia Cart, Deep Blue. Product No: PEL-Color Price: Call for Pricing US Shipping and Billing Only Armstrong Medical Carts Home About Us Contact Us Emergency Standard SteelDrawer Basic Emergency Cart" Beige, Breakaway Lock Model: ABL-BStandard features: Standard 5"swivel, 2locking andtracking heavy-duty casters and a built-in stabilizer bumper give Armstrong carts mobility and stability. Rubber wheels provide smooth, quiet operation. This button will also re-lock the cart if you need to leave it. Armstrong Medical FAX: csr@ SSCOR, INCRandall Street Sun Valley, CA USA Telephone + Fax + Email: info@ techsupport@ Rev.R (03/14) Caution-NoticeSSCOR suction units are not designed or intended for use in extended procedures that require prolonged high vacuum/low All the quality features of an Aluminum PremierTM Cart (except Slide-Thru Side Shelf) Product Options AluminumDrawer Auto-Locking Cart, in. To unlock the cart with the keylock override, simply enter the key, turn and hold Two push handles Armstrong Medical industries incKnightsbridge Parkway P.O. Box Lincolnshire, IL FAX: csr@ The Best Overall Value Around Armstrong Medical Offers: Ask you local Representative for a FREE Demo of our most popular carts Armstrong Medical Also available is the Aluminum Auto-Locking Cart which features manual or automatic locking, up to user codes, and supervisor code for programming. Document: Armstrong Medical Missing: pdf Armstrong Medical Industries Inc. Auto-Locking Cart Operating and Master Code Model Instructions. This Cart is available with Optional Prox Reader.